Specification Sheet (Part# 243560)



The VisiTrace DO is designed to measure dissolved oxygen in the low ppb range in brewing applications, notably during filtration and filling. Adjacent markets are also boiler feed water in power plant . The VisiTrace DO offers all the advantages of Hamilton's optical dissolved oxygen sensors: fast response time and easy maintenance. Improvements compared to conventional electrochemical (amperometric) sensors include flow independence, rapid start-up with no polarization time and implified maintenance. Monitoring in low ppb ranges is essential in many applications such as brewing processes and power plants.

Product Specifications

O-ring Material Surface Quality of Steel	EPDM (FDA approved) Ra < 0.4 μm (N5)
Pressure Range	-1 to 12 bar
Process Temperature	-10 to 140°C; the Sensor provides no DO reading above 85°C
Steam Sterilizable	Yes, max. temperature 140°C
CIP	Yes
Autoclavable	No
Configurable Values	DO: mbar; %-sat; %-vol; µg/l; mg/l; ppb/ppm (gas); ppb/ppm (dissolved oxygen); Temperature: °C, °F, K
Drift at Room Temperature	< 1 % per week @ 100 ppb
Temperature Sensor	NTC 22 kOhm
Response Time	< 20 sec in gas; < 90 sec in water
Required Flow	None
Oxygen Consumption	None
Measuring Range	0 to 2 ppm (0 to 50 mbar)
Measurement Principle	Oxygen dependent luminescence quenching



Product Specifications

Certificate	Yes, with parameter settings and materials used	
Serial Number	Yes	
Diameter	12 mm	
Process Connection	PG13,5	
Electrical Connector	M12	
Analog Interface 1	4-20 mA for DO, programmable	
4-20 mA Accuracy	03 current value 005 mA B	
4-20 mA Current Range	3.5 to 22 mA	
Operating Voltage	18 to 30 VDC	
Electrolyte	None	
Wetted parts	Stainless steel 1.4435, Silicone (FDA approved), EPDM	
a-length	120 mm	
Analog Interface	Two wire sink needs to be powered by external power supply	
Accuracy at 25°C	± 0.5 ppb or 2% whichever is greater	
Membrane / Cap	Delivered with ODO Cap L0	

© 2016 Hamilton Company. All Rights Reserved.

All trademarks are owned and/or registered by Hamilton Company in the U.S. and/or other countries.

Revision: A / 2010-05-11 Printed in the U.S.A.



USA: +1-800-648-5950 Europe: +41 58 610 10 10

Hamilton Company Inc. 4970 Energy Way Reno, Nevada 89502 U.S.A. Tel: +1-800-648-5950 Fax: +1-775-856-7259 sales@hamiltoncompany.com

Hamilton Bonaduz A.G. Via Crusch 8 CH-7402 Bonaduz, Switzerland Tel: +41 58 610 10 10 Fax: +41-58-610-00-10 contact@hamilton.ch

To find a representative in your area, please visit hamiltoncompany.com/contacts